

# Power Your All Day



## 24H



### 6H

Keep working

### 18H

Keep working

Playback per charge

### 19H

Keep working

### 24H

Keep working

With the charging case

- The machine equipment with TEC condenser+air+water,the best cooling system,keep machine works continuously.
- The machine adopts sapphire contact cooling system,temperature of the handle would be -5-3℃ ,The treatment is very comfortable and painless.
- Italy imported pump ,2filters ,1 for impurity separate,another for water soften.
- Suitable for all kinds of hair removal with painless and permanent.

# MULTI-SCREEN LINKAGE

HANDLE WITH LARGE SCREEN, FREE INTERACTION WITH THE MAIN SCREEN, NO DELAY,  
CAPACITIVE SCREEN SYSTEM SLIDING OPERATION



STABILIZE



SMOOTH




HANDLE SCREEN



**1600W diode laser hair removal machine effect of treatment.**

# For all skin types



755nm / 808nm / 1064 nm


## Handle Introduction:

- USA imported gold tin sintering laser 16 bar 1000W, sport size 12\*35mm
- The handle with powerfull cooling effect, increased comforta and reduce pain during treatment.
- The handle equipment with counter show you the exact shorts.



- 1600W diode laser hair removal machine used 14 inch color touch screen.
- Six kinds of skin types option, easy to operate.





## Packaging & Shipping

Packing of machine	Aluminium box with foam ensure product safety
Before the shipment	Machine testing
Delivery time	3-5 working days after payment
Delivery type	Offer door to door service by air such as DHL
Upon receipt of goods	We offered heart to heart services ,warranty 2 years of whole machine

## PACKAGING



Built-in prevention  
Collision bubble



Tight packaging



3-5 business days  
delivery