

Stronger, Faster

×

14-inch HD 4K Screen



Advantage of Diode Laser diode laser 755 808 1064

1. 755 808 1064 nm from Technology .
2. For all skin and hair style removal .
3. Effective for the hair follicles produce heat accumulation, Permanent Painless hair removal.
4. Almost no skin scattering, no harm to the skin and sweat glands, no scar, no any side-effect



5. Air Cooling + Water Cooling +TEC Cooling 3 in 1 System .24 hours working ability ,
6. 12*38mm Big Spot Size ,Reduce treatment time for original 1/5
7. Add Logo and language for free .


12*20mm or 12*35mm handle

Suitable for any unwanted hair on areas like face, arms, armpits, chest, back, bikini, legs...



The new **14-inch 4K** screen

Support system customization



- * 14 inch True Color 4K Screen, offering super cool touching experience.
- * OEM service is accepted. adjusting parameter is ok.
- * Add your logo and language for free

Treatment Effect

This is the clinical result of hair removal
It takes 3--5 times to realize
permanently hair remoavl





Products Description





High-quality laser bars imported from USA

1000/1200/1600w high power



Fast hair removal



▶ 10bar
1000W



▶ 12bar
1200W



▶ 16bar
1600W


**755 808 1064nm Technology of ice platinum is the most advanced technology for hair removal .
Especially for different skin and hair style .**

- * USA Coherent imported laser bar.
- * 10-40 million shots (Newest Golden Laser Bar)
- * 10bar 12bar 16bar ,to choose from .
- * 1000w/1200w/1600w big power,

Specification of Diode Laser Hair Removal Machine

Item	Vertical 755nm+808nm+1064nm diode laser
Laser type	Diode laser,12bars/16bars
Power of each bar	100w
Display system	14 inch true color 4K touch screen
Wavelength	808nm/755nm/1064nm
Spot Size	12*20mm ² /12*35mm ²
Laser handle lifespan	808nm:At least 10-40 million shots
Energy	10-150 J / cm ² adjustable (up to 150J/cm ² optional)
Pulse Duration	40~800ms adjustable
Frequency	1.0-10 Hz;
Cooling system	TEC semiconductor condenser+air+close water circulation
Handle Power	1000w / 1200w / 1600w
Machine Power	3000w
Crystal temperature	-20~3°C
Power requirement	AC220V/110V 50~60Hz

Custom Section



Professional OEM ,ODM Services:

- Print any color .
- Print your logo on the machine .
- Add any language into machine system.
- Design exclusive machine shell for you , form your own brand in market .
- Design new interface and system of machine , make it most convenient to you and your clients.

About Us

We Are 13 Years

Professional high-tech beauty equipment manufacturer in China.

潍坊明亮电子有限公司

坚守客户价值不动摇·让客户满意

坚守员工价值不动摇·让员工成长

Hold Fast to customer's value to make them feel satisfied

Hold Fast to employees' value to let them develop



Mingliangkj in 2007, Through 13 years ,we have built reliable Production ,Quality Control ,Warehousing and Sale&Service department.

Products around world ,including Europe ,North America, Asia and so on .more than 600 clients in more, than 100 countrys all over the world



Packing

Safe and thoughtful packaging service



Built-in prevention Collision bubble

Two-year warranty for machine handle as consumable,
one-year warranty.

OEM&ODM service for distributor.

Tight packaging

Training: (Video+Manual+Online Service)
Can Keep You Operate It Easily.



3-5 business days delivery

Professional guide:
24 Hours Professional online customer service,

About the Shipping

We can offer the door to door services
by air or by sea just depend on your actual request.
Such as DHL,UPS,TNT,FEDEX...

