

NEW ! Technology



Advantage of Titanium 1600W Diode Laser Hair Removal machine

1. 755+808+1064nm diode laser hair removal system uses, Suitable to all skin types of hair removal.
2. Golden laser bars from Germany or USA imported, max 40,000,000 longer lifespan
3. 1600WTEC cooling system, ensure laser works continuously without air conditioner in Summer
- 4.No scar, no any side-effect .
- 5.High power , no pain , 3-5 sessions permanent hair removal

One minute cooling -21°C

Best **TEC Cooling** system
hair remover laser



12*20mm or **12*35mm** handle

Suitable for any unwanted hair on areas like face, arms, armpits, chest, back, bikini, legs...

12*20mm {




12*35mm {



1 minute treatment ☐☐


**NEW !
Technology**





**High-quality
laser bars
imported from
USA**

1000/1200/1600ww high power



Fast hair removal



⌚ 10bar
1000W




⌚ 12bar
1200W



⌚ 16bar
1600W

For all skin types



755nm / 808nm / 1064 nm

The handle equipped with 3 wavelength: Alex 755nm, speed 808nm and long pulse 1064nm

Speed 808nm: Golden standard wavelength for all hair types

Alex 755nm: Specific effective for blonde hair, fine hair

Long Pulse 1064nm: Specific effective for dark, tanned skin



3 in 1 cooling system: Air Cooling + Water Cooling + TEC Cooling 3 in 1 System .24 hours working ability

12*20mm / 12*35 mm Big Spot Size ,Reduce treatment time for original 1/5



Large Spot Size

Quick and Comfortable


With large spot size of $1.2 \times 3.5 \text{ cm}^2$, for faster treatments and better patient experience.



TEC Plus

Continuous Contact Cooling

TEC is an advanced technology that continuously cools skin and facilitates range-controlled temperature throughout the entire treatment. Patients can now enjoy a completely pain-free, cool and comfortable experience throughout the session.



- * 12.4 /14 inch True Color Touching Screen, offering super cool touching experience.
- * OEM service is accepted. adjusting parameter is ok.
- * Add your logo and language for free

Specification of Titanium 1600W Diode Laser Hair Removal machine

Item	Vertical 755nm+808nm+1064nm diode laser
Laser type	Diode laser,10bar 12bars/16bars
Power of each bar	100w/Bar
Display system	12.4 /14 inch true color touch screen
Wavelength	808nm/755nm/1064nm
Spot Size	12*20mm ² /12*35mm ²
Laser handle lifespan	At least 20-40 million shots