

# New Machine

“

**High power diode laser  
with nice cooling technology  
for hair removal with painless!**

”



\*1800w High power diode laser with nice cooling technology, for hair removal with painless!

\* Diode laser enable the light to penetrate deeper into skin and safer than other laser. because it can avoid the melanin pigment in the skin's epidermis, we can use it for the permanent hair removal of all color hairs on all 6 kinds skin types.

\* Suitable for any unwanted hair on areas like face, arms, armpits, chest, back, bikini, legs...It also have the skin renewing.


\* Frequency 1-10hz. treatment fastly!!! Machine for fast and permanent hair removal . Painless!!



755 nm



808 nm




1064 nm



755 nm for white skin (fine, golden hair removal );



808 nm for yellow neutral skin (brown hair removal);



1064 nm for black skin (black hair removal)

### Handle display


1.Three wavelengh diode laser. 2.Golden laser bars from German or USA imporved 40,000,000+ longer lifespan. 3.Safe, Fast, Painless permanent 4.For all skin and hair style hair removal 5.14.0 inch true color touch screen with 6 skin colors.

# Handle Details


Three Wavelengths Work Together



  
**12\*20nm**  
755nm Laser  
808nm Laser  
1064nm Laser



  
**12\*35nm**  
755nm Laser  
808nm Laser  
1064nm Laser



**Waves laser combines 755nm 808nm 1064nm, suits for all skin and hair types treatment.**

755nm for white skin (fine/ golden hair) hair removal.

808nm for yellow (natural) skin hair removal.

1064nm for black skin (black hair) hair removal.

Before and After alma soprano ice platinum diode laser hair removal machine

# For all skin types

**Triple wavelength** laser work together

755  
nm

808  
nm

1064  
nm

755nm/808nm/1064nm

755nm  
808nm  
1064nm

## Laser hair removal treatment theory



Hair active growth phase(3-6years)



laser treatment



Transition phase (1-2weeks)



Resting phase (1-2 weeks)



Return to growth phase

## Product Parameters







Model	808V29
Laser Type	808nm diode laser or 755/808/1064nm 3 waves combined
Display	14 inch 4K touchable screen
Wavelength	755/808/1064
shots	20-40 million shots
Energy	10~150 j/cm <sup>2</sup> , adjustable
Frequency	1-10HZ
Cooling	Compressor+air+water
Power	3500W
Spot size	12*24mm or 12*36mm for choose
Voltage	110V/ 60HZ or 220V/50HZ for choose
Net Weight	95Kg
Gross Weight	105Kg
Machine size	53*40*105cm

Box size 125\*56\*70.4


Before and after effect comparison

# Before and After



Painless hair removal, no side effect☑Make your skin silky and full of charm!  
Screen system display

## 4K high definition screen system






## Operation System

- \* 14.0 inch screen
- \* multi-language system
- \* Easy to operate providing operation skills and teaching services
- \* Free logo and language can be customized on the scr

## Custom Section



Custom section

You can customize your exclusive logo screen according to your needs

Why Choose Us

# Our customers

60000+ CUSTOMERS



102

Countries

OEM/ODM

Customize the machine according to customer needs

CERTIFICATE



14 years manufacturer with rich experience in producing beauty machines!

13 years Alibaba golden supplier

CE certificates approved TUV certificates approved

Personal custom made & OEM

# Customer Feedback

We are NO.1 in feedback of real client



○ Belgium 11,Mar,2021,

Supplier Service: **Very satisfied** (5 stars)

On-time Shipment: **Very satisfied** (5 stars)

**Very satisfied** (5 stars)

**Very satisfied** (5 stars)

2020 Alma Laser Soprano 808nm Hair Removal 755n...



2020 Alma Laser Soprano 808nm Hair Removal 755n...



this is the first time I ordered something from Alibaba and thanks to Jason I had a reaaaallllyy good experience. he gave me all the information/tips about the hair removal machine. the delivery was super fast. and omg the results are amazing !!! (see pictures after one session) i will definitely buy more from Jason!



○ United 07,Feb,2021

Supplier Service: **Very satisfied** (5 stars)

On-time Shipment: **Very satisfied** (5 stars)

**Very satisfied** (5 stars)

**Very satisfied** (5 stars)

2020 Newest Diode Laser 808 nm Alma Soprano ICE ...



2020 Newest Diode Laser 808 nm Alma Soprano ICE ...



im very happy with the machine. Well packed and the machine is Very easy to navi gate!



○ Ukraine 02,Mar,2021

Supplier Service: **Very satisfied** (5stars)

On-time Shipment: **Very satisfied** (5stars)

**Very satisfied** (5stars)

**Very satisfied** (5stars)


12 bar 1200W 3 waves laser hair removal machine



12 bar 1200W 3 waves laser hair removal machine



Great seller. The product is as specified. He is very emotional, explains everything, sends photos, videos, if something is not clear. I highly recommend! You can or der safely, do not worry, everything will be fine. Thank you seller for your product a nd support! 🙏👍😊



○ Sweden 02,Jan,2021

On-time Shipment: **Very satisfied** (5 stars)

Supplier Service: **Very satisfied** (5 stars)

**Very satisfied** (5 stars)

**Very satisfied** (5 stars)

2020 Double Handles Alma Soprano Titanium Diod



2020 Double Handles Alma Soprano Titanium Diode L...



I am very happy with my machine 😊👍  
To start from the beginning, the whole communication and explanation of transpo rt to how the machine works I am super happy.  
Viki has helped me a lot, she is the Best.  
I bought a hair remover machine and am very happy with the results that the mac hine gives already after the first treatment.  
The machine came very well packed in a box and with instructions from Viki I st rted working with the machine immediately 📄  
I have made my best purchase ever, will only buy from them machines.  
Grateful for all the help and support.  
Will buy more machines from her.



## Product packaging

The aluminum box packaging machine is sturdy and durable, with safety protection, helping your machine get home safely!

# PACKING

Safe and thoughtful packaging service



Built-in prevention  
collision bubble

Two-year warranty for machine  
handle as consumable,  
one-year warranty

Tight packaging

Training:  
(video + manual + online service)  
can keep you operate it easily



3-5 business days  
delivery

professional guide:  
24 hours professional online  
customer service

