



Portable household hair removal machine advantages

- 1) Show that the overall volume of the machine is very small.
- 2) The display handle is small, 168g handle is very light
- 3) The machine is a compressor with high refrigeration efficiency and low noise
- 4) The machine is light and easy to carry

Machine Parts



Handle Display

*The handle is small and light, weighing as low as 168.8g.
Very light to operate*



Machine Display



Left 45°



Positive



Right 45°

Mini Diode Laser handle, spot size 14*14mm, 5 bars 600w

Cooling Effect

The handle has a cooling effect that improve treatment comfort.



Just One minute!

Quick cooling down to

-25°C

1) Diode laser 755nm+808nm +1064nm hair removal for all skin types

2) Water cooling+Air cooling+compressor cooling , for painless hair removal.

Working Principle

755nm and 808nm and 1064nm , suits for all skin and hair types.



ALEX 755nm

For white skin

(fine, golden hair removal)



SPEED 810nm

For yellow neutral skin


(brown hair removal)



YAG 1064nm

For black skin


(black hair removal)



Screen Display

13.3 inch 4K true color touch screen

The display screen is clear at a glance and easy to operate



6 language for your choice. Super cool touch Experience .

Special language can be added according to your actual requirements.

Your logo also can be added on diode laser screen.

1. 13.3 inch touch screen, humanized designed
2. Male/female, body parts, 6 skin types for option.
3. English+your native language.
4. Free OEM program service (logo/system...)

We have OEM Services

Serving your needs



Our factory

Weifang Sunshinekj electronics Co., Ltd (abbreviation:MLKJ) is a highly professional and experienced manufacturer of beauty equipment in China,has 14 years in beauty industry

13 Years Laser Beauty Device Manufacturer

- High Feedback
Top10 Supplier
- **OEM & ODM**
SERVICE



13 Years Laser Beauty Device
Manufacturer



• High Feedback
Top10 Supplier

• OEM & ODM
SERVICE

Premium OEM Factories

High-performance manufacturing capacity
R&D capability for customization
Professional certifications and approvals

2. We have professional Production R & D department, Can provide technical support □ 2 year warranty



Product packaging

Packing

safe and thoughtful packaging service



Built-in prevention Collision bubble

Two-year warranty for machine handle as consumable,
one-year warranty

OEM&ODM service for distributor.

Tight packaging

Training: (Video+Manual+Online Service)

Can Keep You Operate It Easily



3-5 business days delivery

Professional guide:

24 Hours Professional online customer service