

# Diode Laser



15 Bar **1800W** Handle

\*Increase the treatment head of nasal hair  
and treat small parts easily




## Advantages of diode laser hair removal

- \* High power diode laser with nice cooling technology, for hair removal with painless!
- \* Diode laser enable the light to penetrate deeper into skin and safer than other laser. because it can avoid the melanin pigment into the skin's epidermis, we can use it for the permanent hair removal of all color hairs on all 6 kinds skin types, including the tanned skin.
- \* Suitable for any unwanted hair on areas like face, arms, armpits, chest, back, bikini, legs...It also have the skin renewing and skin tightening at the same time.
- \* Frequency 1-10hz. treatment fastly!!! Machine for fast and permanent hair removal . Painless!!

# Working Principle

Suits for all skin and hair types



- **755nm for white skin** (fine, golden hair removal )
- **808nm for yellow neutral skin** (brown hair removal)
- **1064nm for black skin** (black hair removal)



- \* Spot size 12\*20mm, 12\*35mm,for option
- \*450g handle, light weight, free quick slide treatment
- \* With indicator light, to show working condition(on machine & handle), safely use


## Treatment Effect

This is the clinical result of hair removal  
It takes 3--5 times to realize  
permanently hair removal



### Machine Program of diode laser

1. 12.4 inch big screen, quick touch
2. Male & female, 6 body parts, 6 skin types setting smart software
3. 6 language options, your native language can be added
4. Free OEM program service (logo/system...)




Product name	Laser Ice platinum hair removal machine
Laser bar	Germany/USA imported, 10 bar, 12 bars, 16 bars
Wavelength	755nm 808nm 1064nm
Energy	0-150J/cm <sup>2</sup>
Frequency	1-10hz
Pulse width	40-800ms
Operative LCD Interface	12 inch True Color touch screen
Cooling system	Air and Close Water Circuitation Treatment head with semiconductor cooling temperature adjustable
Power	4000W
Electrical source	220V/50HZ or 110V/60HZ



# RESEARCH AND DEVELOPMENT

## Weifang Mingliangkj electronics Co., Ltd

We have professional Production R & D department, From design research and development to production, every step is strictly checked to ensure product quality.



## CERTIFICATE DISPLAY



# Packing

safe and thoughtful packaging service



## Built-in prevention Collision bubble

Two-year warranty for machine handle as consumable,  
one-year warranty.

**OEM&ODM service for distributor.**

## Tight packaging

Training: (Video+Manual+Online Service)  
Can Keep You Operate It Easily.



## 3-5 business days delivery

Professional guide:  
24 Hours Professional online customer service,