



808 Diode Laser

Big Power: 1000w 1200w 1600w

Triple wavelength: 755nm 808nm 1064nm

For different skin type: white, brown ,black

Products Description

Machine Parts



Product Name

Portable diode laser hair removal machine

Laser type

755nm/808nm/1064nm

6laser bar	8 bars/10 bars/12 bars/16 bars , imported from Germany/USA
Output power	800w/1000w/1200w/1600w
Display system	10.4 inch true color touch screen
Laser handle shots	40 million times
Energy	10~150 j/cm2, adjustable
Pulse Duration	10~300ms adjustable
Frequency	1~10Hz
Power	2500w
Crystal temperature	-29~5°C



Advantage

1. Advanced Tech: Gold tin sintering technology,
2. Handles: Germany/USA laser bars 8—16bars 800—1600W power for faster and better hair removal, real painless and permanent hair removal, with obvious results.
3. Fast treatment: big spot size / 12*20mm / 12*35mm, frequency 1-10Hz, higher efficiency
4. Continuous working : TEC condenser +air +water+ semiconductor cooling system

Handle display

Handle display Handle color optional

weight **450g**

The handle weighs only 450g, making the treatment process easier

Cooling effect

Fast cooling, more comfortable treatment process



12*20mm



12*35mm



12*20mm




12*35mm

Most advanced TEC cooling system inside this machine to deliver a super good cooling results.

24 hours working time. Sapphire material. Actual Pain-free experience!

Laser show Handle laser bar optional



Speed Diode Laser 808nm: Golden standard wavelength for all hair types laser hair removal
755nm: Specific effective for blonde hair, fine hair laser hair removal
ND YAG 1064nm: Specific effective for dark, tanned skin

Before and After

Treatment comparison



Product Display



For more product details, consult immediately!