

Portable Yag Laser / Q Switched Nd Yag Laser / Nd Yag Laser Machine

ND YAG Laser



1. Mainly Usage:

- 1). ND YAG laser : tattoo/eye embroidery/eyeline/freckles removal and skin whitening.
- 2). 1064nm wavelength: get rid of freckles and yellow brown spot, eyebrow tattoo, failed eye line tattoo, tattoo, Birthmark and Nevus of Ota, pigmentation and age spot, nevus in black and blue, scarlet red, deep coffee and etc. deep color.
- 3). 532nm wavelength: get rid of freckles, eyebrow tattoo, failed eye line tattoo, tattoo , lips line, pigment, telangiectasia in shallow red, brown and pink and etc. light color. pigment removal.
- 4). 1320nm: Professional for skin rejuvenation and face deep cleaning , blackhead removal, skin tightening and whitening, skin rejuvenation.

6⁺ COLOR OPTIONS

To meet the needs of more customers



2.The Handle Details:

Having 5 professional treatment heads,

- 1). Adjustable 1064/532nm filter.
- 2). Fixed 1064/532nm filter.
- 3). 1320nm(optional)

5 therapeutic **Heads**

■ 532 & 1064: removing tattoo, eyeliner and lip line

■ 1320: black-faced doll whitening and whitening skin

■ Adjustable 532 & 1064: removing large-area tattoos



Adjustable
532nm



Adjustable
1064nm



Black doll
1320nm



Fixed
532nm




Fixed
1064nm

3. Screen Of Interface:

If not clear ,pls just contact with me ,

I will send you more details clearly ,and having clear movies of operating .



4. Accessory and Packing:



Model	SSKJ-Q Switch ND YAG laser Machine- A1
APPLICATION	1)tattoo removal 2)eyebrow removal 3)eyeline removal 4) lipline removal 5)pigment treatment 6)birth mark removal 7)nevus of ota removal 8)skin whitening 9)skin rejuvenation
wavelength	1064&532&1320
Width of pulse	0-10ns
frequency	1-10HZ
probe	3 fixed probes 1064&532&1320nm 2 adjustable probes 1064&532nm
Aimring dot	YES
Handle shots	More than 1 million shot time
Power supply	220V/6A or 110V/12A
Packing method	Aluminum box
N.W	20KG
G.W	30KG
Machine size	38*39*50cm (L*W*H)
Package size	46*49*60cm (L*W*H)
color	White, black ,silver, white+black..or other color as your inquiry

Our Services

Heart to heart services:

1) Warranty:

2 years warranty ,Lifelong free maintenance.

2) Training:

Professional training offered to ensure every customer own the professional operation knowledge in time,

Companion and DVD for training will be sent together with the machine,

Online training directly is ok.

No any charge, for free!

3) Free logo,lauguage,color design:

Your **own logo** can be added on the machine screen for free.

Your **lauguage** can be added in the screen for free.(more convenient to operate)

Various colors of shell to choose from . just choose the one you prefer.

4) Delivery Time:

Enough producing line ,every machine will be sent **within 3 working days.**

and transported via DHL/UPS/Fedex .etc.(3-5 days from me to you door to door)

Shipping&Packaging

Delivery time	Within 3 working days after deposit
Delivery way	Air transportation,and express such as DHL UPS TNT..
Before delivery	Test every details of the machine,keep the machine working well
After delivery	Warranty: 2 years ,offer impeccable after-sale service

Package	Aluminum Box with Foam inside ,and Wheels Outside
----------------	--





Built-in prevention
Collision bubble



Tight packaging



3-5 business days
delivery