

## Advantages

- \* USA or Germany Dilas imported laser bar.
- \* More than 40 million shots , more than 3 years don't need to change new handle.
- \* 3 waves 1064nm +808nm + 755nm, 3 in 1 all skin type can be used
- \* High power: NEW 1000W/ 1200W /1600W handle for options
- \* Medical handle spot size 12\*24mm, 12\*36mm, face & body hair removal solution!
- \* Cooling system: Unique Dual- TEC cooling system, most effective to ensure machine work all day, 24hr no down time.
- \* Long life: 40 million shots

**350g** lightweight **handle**, more ergonomic

Available in **black or white**



## Handle Display

- 1200w ,1800w big power for free choice
- 12\*24 or 12\*36 mm spot size
- \*350g Medical handle, light weight, free quick slide treatment
- \* With indicator light, to show working condition(on machine & handle), safely use



### 1. Cooling of ice platinum

- \* Turn on machine, immediately cooling , immediately hair removal
- \* Good cooling longer handle lifespan
- \* Real ice painless hair removal effect

**12\*24mm or 12\*36mm** handle

Suitable for any unwanted hair on areas like face, arms, armpits, chest, back, bikini, legs...




### 2. Safety Use On All Skin Type


1. Alex 755nm for light skin

2.Speed Diode 808nm for yellow skin

3.Long Pulse 1064nm for darker skin



### 3.Treatment Effect



## Hair removal comparison

The real picture taken by the customer

Different parts of men and women, as well as different skin colors can have very good hair removal results, they all get a permanent and painless hair removal experience



Before



After Treatment

### 4.Screen Display Machine Program

1. 14 inch big screen, quick touch
2. Male & femal, 6 body parts, 6 skin types setting smart software
3. 6 language options, your native language can be added
4. Free OEM program service(logo/system...)

### 5.OEM / ODM Service

- >>OEM your own machine body
- >>OEM your own program software
- >>OEM pretty machine colors
- >>Print your LOGO on machine body and screen
- >>R & D team and Quality inspection Show

### 6.Certificate Display



# Build more trusted partners

## Our customers

60000+ CUSTOMERS

## OEM/ODM

Customize the machine according to customer needs



## CERTIFICATE


Obtained multi-way authoritative certification,  
product testing certification, product patent authority,



R & D design Design and development teams from the United States and Germany.  
Standard production line.Certified and tested mature production line and quality inspection  
team. What we care about most is High-quality products are the standard for maintaining  
cooperation.

# SHIPPING

Welcome to visit our factory



## In terms of following trade details:

- 1)The shipping cost are based on DHL cost to your country
- 2)Delivery time:3-5 days after receiving payments.
- 3)Payment terms:T/T(bank transfer),Western Union.
- 4)Warranty:2 years for the whole machine
- 5)Warranty Policy:one month guarantee replacement (we bear all shipping cost),2years warranty,lifelong maintenance.
- 6)Packing method: Aluminum box with hard plastic foam.
- 7)Free-training to customers:Free We could offer DVD and User's manual and 10 Hours online service to our customers
- 8)Certifications:CE TUV ISO 13485
- 9)MOQ:1 UNIT
- 10)The quotation here above is valid within 1 month