



Treatment of Alma Soprano Ice Platinum Laser hair removal machine

1. Alma Laser technical, suits for all skin and hair types.
2. Handles: 1000W or 1200W, one spot size 12\*20mm, the other 12\*35mm
3. Fast treatment: 1-10Hz frequency, USA imported laser bars.
4. Continuous working 12h: Air+water+unique 1200W TEC cooling system, controls steady water temperature 24°C, ensure machine works continuously all the day, even in summer without air-conditioner laser hair removal machine



Handle of Soprano Titanium Laser hair removal machine Alma Soprano Ice Platinum

1.12\*20mm handle can you on small parts of the body, such as face hair removal and other samll place.

2.12\*35mm can use at large parts of the body, such as back, arm and leg

3.With imported USA laser stack, strong energy, longest lifespan. the best laser in this line laser hair removal machine

**350g** lightweight **handle**, more ergonomic



Available in **black or white**





High-quality  
**laser bars**  
imported from  
**Germany**

1000/1200/1600ww high power


Fast hair removal



⊙ 10bar  
**1000W**




⊙ 12bar  
**1200W**



⊙ 16bar  
**1600W**

- >>Germany Emitter, strong energy
- >>1200W power of hair removal on the whole body;
- >>1-10Hz fast frequency
- >> Italy water pump, it can keep machine working 24 hours without stop.



### 755nm hair removal



### 808nm hair removal



### 1064nm hair removal



Screen of Soprano Ice Platinum Laser hair removal machine

- 1) Touch Screen: 12.4/14 inch easy to operate.
- 2) 6 language for your choice.
- 3) Color for choose, also your LOGO could be put on screen and machine shell for free

