



1. Three wavelength diode laser.
2. Golden laser bars from German or USA imported 40,000,000+ longer lifespan.
3. Safe, Fast, Painless permanent
4. For all skin and hair style hair removal
5. 14.0 inch true color touch screen with 6 skin colors.



---USA imported laser bar, can shot 20-40 million times

---Laser technology, 3D 755+808+1064nm or speed diode 808nm

---Big power, 1000w, 1200w and 1600w for choice, each bar is real 100w

---Big spot size 12\*20mm, 15\*25mm, 12\*38mm for option

---Very light handle, only 450g, it will be more convenient for you to hold it to do the treatment

---Good ice cooling, achieve pain free treatment



# MACHINE DETAILS DISPLAY

EXQUISITE DETAIL DISPLAY




**About Handles**



### Safety Use On All Skin Type

1. Alex 755nm for light skin
2. Speed Diode 808nm for yellow skin
3. Long Pulse 1064nm for darker skin





- **755nm for white skin** (fine, golden hair removal )
- **808nm for yellow neutral skin** (brown hair removal)
- **1064nm for black skin** (black hair removal)

## Product Paramenters



|                     |  |
|---------------------|--|
| Pulse duration      | 10-300ms adjustable                                  |
| Crystal temperature | -27°C~5°C  |
| Laser bar           | 10bar/12bar/16bar,imported from Germany/USA          |
| Technology          | Tripe waves 755+808+1064nm Technology                |
| Output power        | 1000w/1200w/1600w                                    |
| Laser Type          | 808nm diode laser or 755/808/1064nm 3 waves combined |
| Display system      | 12 inch screen                                       |
| Wavelength          | 755/808/1064   |

|           |                                    |
|-----------|------------------------------------|
| shots     | 20-40 million shots                |
| Energy    | 10~150 j/cm2, adjustable           |
| Frequency | 1-10HZ                             |
| Cooling   | Compressor+air+water               |
| Power     | 3500W                              |
| Spot size | 12*20mm or 12*35mm for choose      |
| Voltage   | 110V/ 60HZ or 220V/50HZ for choose |

## Screen Display



## Machine Program

1. 12 inch big screen, quick touch
2. Male & femal, 6 body parts, 6 skin types setting smart software
3. 6 language options, your native language can be added
4. Free OEM program service(logo/system...)

## Comparison chart before and after hair removal effect

