



Safe Efficient Quick

DIODE LASER

Hair Removal

Laser painless hair removal
Triple waves: 755nm/808nm/1064nm
Suitable for all skin types

This product is based on diode laser technology for hair removal, which is safe and efficient. The beam emitted by the diode laser machine will penetrate the skin surface and eventually be absorbed by the hair follicle, and through the selective absorption of the laser energy, the hair follicle is damaged and can no longer grow hair, while not damaging the surrounding tissue. The process of freezing laser hair removal is simple and fast, and generally leaves no scars after treatment. Freezing laser hair removal can be permanent hair removal, generally 3-5 times can be permanent hair removal. The freezing laser is the most advanced permanent hair removal method, which has obvious hair removal effect, fast operation speed, light pain, no side effects on the human body and almost no impact on the skin.



DIODE LASER

STRONGER SMARTER FASTER

SUPER ICE PAINLESS EXPERIENCE
PERMANENT HAIR REMOVAL
COMFORTABLE HAIR REMOVAL

Rapid cooling, only 30s

1 minute hair removal

Suitable for all skin color hair removal, including tanned skin

755nm for white skin (fine/ golden hair) hair removal.

808nm for yellow (natural) skin hair removal.




1064nm for black skin (black hair) and tanned skin hair removal.

Applicable to all treatment sites



Bar function


3 kinds of wavelength function



755 nm for white skin (fine, golden hair removal);



808 nm for yellow neutral skin (brown hair removal);



1064 nm for black skin (black hair removal)

ICE PLUS continuous cooling system.The treatment process is more comfortable.
It can work continuously for 24 hours.



Just One minute!
Quick cooling down to **-25°C**



The latest plug-in design can treat difficult to reach small body parts, such as nose hair, eyebrows, auricle and so on !

BEFORE AND AFTER TREATMENT

MAKE YOUR SKIN SILKY AND FULL OF CHARM!






Machine Program

1. 14 inch big screen, quick touch
2. Male & femal, 6 body parts, 6 skin types setting smart software
3. 6 language options, your native language can be added
4. Free OEM program service(language/logo/system/color...)

The new **14-inch 4K** screen

Support system customization



Technical parameter

Model	Diode laser D18
Laser Type	Germany/USA imported, 8--16 bars
Display	14----15.6 inch 4K touchable screen
Wavelength	808nm or 755nm+808nm+1064nm
Shots	40 million shots
Energy	10~150 j/cm2, adjustable
Frequency	1-10HZ
Cooling	High Speed Double TEC coolingAir and Close Water Circulation Treatment head with semiconductor cooling temperature adjustable
Power	3500W
Spot size	12*20mm/12*35mm for choose
Voltage	110V/ 60HZ or 220V/50HZ for choose

FDA certified, professional quality

Establishment Registration & Device Listing

FDA Home Medical Devices Databases



New Search	Back To Search Results
<p>Establishment: WEIFANG MINGLIANG ELECTRONICS CO.,LTD. Floor 3, Building 4,Second Accelerator, Yuqing Eastern Street, High-Tech District Weifang Shandong, CN 261000 Registration Number: 3007549439 FEI Number*: 3007549439 Status: Active Date Of Registration Status: 2022</p> <p>Owner/Operator: Weifang Mingliang Electronics CO.,LTD. Floor 3, Building 4,Second Accelerator, Yuqing Eastern Street, High-Tech District Weifang, Shandong CN 261000 Owner/Operator Number: 10082104</p> <p>Official Correspondent: Pingping Lv Floor 3, Building 4,Second Accelerator, Yuqing Eastern Street, High-Tech District Weifang, Shandong CN 261000 Phone: 86-10-56335780</p> <p>US Agent: Wen Xu 4611 Maydew Mews Way Ellicott City MD Ellicott, MD US 21042 Phone: 443 8968583 Ext Email: Infor@Believe-Med.Com</p> <p>* Firm Establishment Identifier (FEI) should be used for identification of entities within the imports message set</p>	



Page Last Updated: 05/09/2022

Note: If you need help accessing information in different file formats, see Instructions for Downloading Viewers and Players.

Language Assistance Available: Español | 繁體中文 | Tiếng Việt | 한국어 | Tagalog | Русский | العربية | Kreyòl Ayisyen | Français | Polski | Português | Italiano | Deutsch | 日本語 | فارسی | English

Exceeding
Your Expectations

The Most
Professional
Beauty Machine
Customization Service



15 years beauty instrument manufacturer, to provide you with more professional and comprehensive technical support and customized services!

Training

- * Manual + Video+Parameter
- * Online Training
- * Beauty Teacher answering
- * Local customers support

Service

- * Warranty: 2 years for machine , 1year for handle (no limited of shots)
- * After-sale Phone to keep contact.
- * OEM service

Delivery time: 3-7 working days after payment

Delivery way: by air, DHL , TNT , Fedex, or delivery agent

Before delivery: testing video and pictures

After delivery Warranty: 2 years,offer impeccable after-sale service

Want to know more, welcome to consult! 7*24 hours online!