



Diode laser hair removal

*Big Power: 1200w 1800w
Triple wavelength: 755nm 808nm 1064nm
For different skin type: white, brown, black*

15 years factory, 2 years warranty, 102 countries, 60,000+ customers

MLKJ——Make Your Beauty Business More Easier



Facial TIP!

diode laser hair removal



Easily treat areas that are normally hard to reach!

Improved Reach

This unique facial head allows you to reach areas of difficult access such as ears, nose, and interlining, among others.

ICE with cold Sapphire tip, protects the epidermis while keeping the heat in the dermis, where the follicles are located.

Facial TIP:

Specifications: Diode, 808 nm, Spot Size $\Phi 6$ mm




Diode laser hair removal

Easily treat areas that are normally hard to reach!

Improved Reach

This unique facial head allows you to reach areas of difficult access such as ears, nose, and interlining, among others.

ICE with cold Sapphire tip, protects the epidermis while keeping the heat in the dermis, where the follicles are located



Advantages

- 1. 3 waves 1064nm + Diode 808nm + 755nm, 3 in 1 all skin type can be used
- High power: NEW 1000W/ 1200W /1600W handle for options
- 2. Big spot size 15*25mm, 12*35mm face & body hair removal solution!
- 3. Cooling system: Unique Dual- TEC cooling system, most effective to ensure machine work all day, 24hr no down time.
- 4. Long life: double life support guarantee

Newest 100w each bar, new upgraded handle, weight 350g, easy to do treatment.

8 bar 800w; 10 bar 1000w; 12 bar 1200w; 16 bar 1600w



Diode laser hair removal:

- »»Safety: No skin scald, no harm to the skin and sweat glands, no scar, no any side-effect.
- »»Quick: big spot size 12*38 mm², effective and quick treatment on big treatment area

»»Permanent hair removal: remove all hair on all skin types, including tanned skin.

»»Crystal temperature: $\sim 5-3^{\circ}\text{C}$, reduce the pain and increase comfortable sense in treatment.



Hair removal principle

Make Your Beauty Business More Easier





The laser selectively acts on the melanin in the hair follicle, destroying the hair-growing area

Natural hair loss, prevent regeneration, and achieve the purpose of hair removal

Hair removal also stimulates collagen regeneration, shrinks pores and makes skin firm and smooth


1. Painless hair removal, no side effect.
2. Strong power, Germany imported laser diode module, 10bar, 12 bars, 16 bars available.
3. Big spot size 12*20 mm or 12*35 mm, for fast hair removal.
4. Best cooling system: air + water + TEC semiconductor condenser, Water temperature can be controlled between 26°C — 28°C , 24 hours continuously working.



755 nm for white skin (fine, golden hair removal);



808 nm for yellow neutral skin (brown hair removal);



1064 nm for black skin (black hair removal)

Handle Long life time 20-40 millions shots

Speed 808nm: Golden standard wavelength for all hair types

Alex 755nm: Specific effective for blonde hair, fine hair

Long Pulse 1064nm: Specific effective for dark, tanned skin best quality ipl shr
opt laser/ nd yag /alexandrite laser hair removal machine price



handle weighs only 350g

Available in **black or white**



Suitable for diode laser hair removal on all skin of the body
Good Effect of Diode laser hair removal

Model	diode laser 808nm laser hair removal 1200w
Laser Type	808nm diode laser or 755/808/1064 3 wave

Display	14 inch touch screen system
Wavelength	808nm or 755/808/1064nm
shots	40 million shots
Energy	10~150 j/cm2, adjustable
Frequency	1-10HZ
Cooling	Double TEC cooling
Power	3000W
Spot size	12*36mm or 12*24mm for choose
Voltage	110V/ 60HZ or 220V/50HZ for choose
Net Weight	46kg
Gross Weight	80kg
Machine size	53*40*105cm
Model	laser hair removal machine

- 1)Screen can add your own logo
- 2)screen with 6 languages
- 3)different body parts for choose, one touch can start your treatment

Frequency	Pulse	Energy	Total	Date
5	30	78	0	2023-05-08 11:25:11
5	30	78	0	2023-05-08 11:25:13
5	30	78	0	2023-05-08 11:25:17
5	30	78	0	2023-05-08 11:25:19

Multimedia Control System

Supports Bluetooth /Wifi /Remote control and locking/Cloud storage



Establishment Registration & Device Listing

FDA Home Medical Devices Databases



New Search

Back To Search Results

Establishment:

WEIFANG MINGLIANG ELECTRONICS CO.,LTD.
Floor 3, Building 4, Second Accelerator, Yuqing Eastern Street, High-Tech District
Weifang Shandong, CN 261000
Registration Number: 3007549439
FEI Number*: 3007549439
Status: Active
Date Of Registration Status: 2022

Owner/Operator:

Weifang Mingliang Electronics CO.,LTD.
Floor 3, Building 4, Second Accelerator, Yuqing Eastern Street, High-Tech District
Weifang, Shandong CN 261000
Owner/Operator Number: 10082104

Official Correspondent:

Pingping Lv
Floor 3, Building 4, Second Accelerator, Yuqing Eastern Street, High-Tech District
Weifang, Shandong CN 261000
Phone: 86-10-56335780

US Agent:

Wen Xu
4611 Maydew Mews Way Ellicott City MD
Ellicott, MD US 21042
Phone: 443 8968583 Ext
Email: Infor@Believe-Med.Com

* Firm Establishment Identifier (FEI) should be used for identification of entities within the imports message set

Page Last Updated: 05/09/2022

Note: If you need help accessing information in different file formats, see Instructions for Downloading Viewers and Players.

Language Assistance Available: Español | 繁體中文 | Tiếng Việt | 한국어 | Tagalog | Русский | العربية | Kreyòl Ayisyen | Français | Polski | Português | Italiano | Deutsch | 日本語 | فارسی | English

Packing

safe and thoughtful packaging service



Built-in prevention Collision bubble

Two-year warranty for machine handle as consumable,
one-year warranty.

OEM&ODM service for distributor.

Tight packaging

Training: (Video+Manual+Online Service)
Can Keep You Operate It Easily.



3-5 business days delivery

Professional guide:

24 Hours Professional online customer service,