

Products Description

1200W + 1800W hair removal machine


1. technical, suits for all skin and hair types.
2. Handles: Spot size 12*24mm, the other 12*36mm
3. Fast treatment: 1-10Hz frequency, USA imported laser bars.



Handle of hair removal machine

1. 12*24mm handle can you on small parts of the body, such as face hair removal and other samll place.
2. 12*36mm can use at large parts of the body, such as back, arm and leg.....

Working Principle



Triple wavelength included: 755nm 808nm 1064nm

755nm suitable for light skin hair removal .

808nm suitable for neutral skin hair removal .

1064nm suitable for black skin hair removal .



We can help you

You will see good results after 3 treatments.

- * Painless
- * Permanent
- * No downtime
- * No side-effects



Screen Display

4K 14 inch HD screen system



- 1) Big size: used 14 inch color touch screen.
- 2) Multiple language: three kinds of skin types option, easy to operate.
- 3) OEM service: your logo can be added on machine screen for free, accept your special language.

Product display



Laser bar	Germany/USA imported 8~16 bars
Wavelength	755nm 808nm 1064nm
Laser Power	1200W + 1800W
Spot size	12*24mm & 12*36mm
Energy	0-150J/cm ²
Frequency	1-10Hz
Pulse width	0-300ms
Operative Interface	14 inch True Color touch screen
Electrical source	220V/50HZ or 110V/60HZ

Certificate display

Certificate is the best guarantee for you



Why Choose Us

- 1) 14 years factory manufacturer . 13 years golden supplier in alibaba .
- 2) 100% good feedback from all customers .
- 3) After-sale team who can solve problems easily .

COMPANY PROFILE

Shandong Saint Lancy Laser is a professional beauty device company specializes in the development, production, sales and service of beauty equipment,

- *755+808+1064nm Ice Cooling Diode Laser Series,
- * Newest Soprano ice platinum Titanium Series,
- * multi-function series 2 in 1 , 3 in 1, 6 in 1 series, Elight series,
- * Q Switch ND YAG laser series,
- * Fat lossing :Cryolipolysis, RF series ,Cavitation and so on.

All the products are taking with CE/ISO certification ,suitable for world market , mainly used on North America ,South America , Europe ,more than 102 countrys ,

14 years factory ,14 years focusing on the development of beauty equipment, Pursuit of higher product quality, Making your business easier!



14 years factory



2 years warranty



132 countries



60000+ customers



We can offer the door to door services by air or by sea just depend on your actual request.Such as DHL,UPS,TNT,FEDEX.



OUR CUSTOMERS



Packing

safe and thoughtful packaging service



Built-in prevention Collision bubble

Two-year warranty for machine handle as consumable,
one-year warranty.

OEM&ODM service for distributor.

Tight packaging

Training: (Video+Manual+Online Service)

Can Keep You Operate It Easily.



3-5 business days delivery

Professional guide:

24 Hours Professional online customer service,