

***2in1 multifunctional combined  
hair removal machine***

*Hair removal and skin rejuvenation  
One machine double effect*



**808+Elight**

**Descrição dos produtos**

# Real shot display

---



808 handle



Elight handle



## **Laser de diodo Elight/IPL manipula em uma máquina**


Salão multifuncional favorito Ipl elight pele macia e remover sardas máquina de depilação a laser de diodo

\* Cabo Elight usa lâmpada do Reino Unido, 150.000-30.000 fotos


\*Laser de diodo: 755nm808nm1064nm

## *Three wavelengths work together*

**12\*24mm<sup>2</sup>** {




**12\*35mm<sup>2</sup>** {



**Suitable for hair removal on any part of the body,  
Such as arms, legs, face, armpits, back, chest, etc.**





# ELIGHT HANDLE

## specification

- High-quality: Elight handpiece with super cooling system
- Optional Spot Size 15\*50mm, 15\*35mm
- Long shots time: 150000 times
- 7 filters: 420/510/560/585/640/690/755nm  
Standard: 420/510/680nm



## Before and after



Skin rejuvenation



Freckle removal



wrinkle reduction



Acne clearance



Hair removal



Pigmentation treatment

## Hair removal and skin rejuvenation one machine and two effects

*2in1 Multifunction*



### **808 handle**

Painless hair removal, Permanent hair removal,  
Suitable for all skin tones.



### **Elight handle**

Elight for hair removal, skin rejuvenation,  
vascular therapy, pigmentation therapy, acne therapy.

# 7-ADVANTAGE

## • Counter

The handle is equipped with an energy counter to clearly understand the total count during use.



## • German imported laser

808 handle adopts Germany imported laser, which has stronger energy and long service life.

## • Big spot size

808 handle uses large light spot of 12× 35 mm, with large processing area and higher working efficiency. The E light handle uses a 15 × 50 mm large light spot.



808 handle

E light handle

## • Cooling Effect

The handle adopts refrigeration effect, which can effectively cool the skin in the treatment process and improve the comfort of treatment.

## • E light lamp

The e light handle uses IPL lamps imported from the United Kingdom, which emit light up to 150,000 times and have a longer service life.




## • Rf function

The e light handle is added with RF function, and the RF function after depilation can achieve the effect of tightening and lifting.

## • Optical filter


The e light handle is equipped with seven filters, which can be used for different treatments and different skin colors to select the corresponding filters, thus making the operation more convenient.



# 14inch true touch screen

6 kinds skin type for choice. accept ODM OEM Service.

The new **14-inch** screen is clear easy to operate.



**Para obter mais informações sobre a introdução do produto e detalhes de uso, consulte-nos imediatamente**

**On-line 24 horas!!**