

MLKJ

CUSTOMER SERVICE

15 YEARS FACTORY, 2 YEARS WARRANTY, 102 COUNTRIES, 60,000+ CUSTOMERS.

MLKJ—MAKE YOUR BEAUTY BUSINESS EASIER



15 years factory



2 years warranty



102 COUNTRIES



2 years warranty




14 inch
Screen Size



3000W
Input power



1-10HZ
Frequency



755nm 808nm 1064nm
Wavelength

>>Machine 14-inch large screen

>>3000W machine Poder to ensure the treatment effect

>>1-10Hz fast Frequência and 15x25mm Tamanho do ponto ensures faster, smooth and effective treatment

>>808 single wave or 755nm/808nm/1064nm perfect triple Comprimento de ondas

>>Easy to operate Data Base system,can do the treatment by man mode and women mode, também diferentes partes do corpo. Para garantir um parâmetro seguro para o novo operador

>> Long life time More than 40 millions tiros gold laser diode module, anti high temperature.

350g lightweight **handle**, more ergonomic

Available in **black or white**





A alça pesa apenas 350g, o que é conveniente para o tratamento

- >>12 pieces or 16 pieces Germany Dilas original laser bars,600/800W/1200W power is capable to meet all demands of hair removal on the whole body;
- >>1-10Hz fast frequency and 15x25mm spot size ensures faster, smooth and effective treatment;
- >Super sapphire touch Resfriamento system ensures painless and comfortable treatment;



Hair removal principle

Make Your Beauty Business More Easier



The laser selectively acts on the melanin in the hair follicle, destroying the hair-growing area

Natural hair loss, prevent regeneration, and achieve the purpose of hair removal

Hair removal also stimulates collagen regeneration, shrinks pores and makes skin firm and smooth



- 755 nm for white skin (fine, golden hair removal);
- 808 nm for yellow neutral skin (brown hair removal);
- 1064 nm for black skin (black hair removal)

Lidar com tempo de vida longa 20-40 milhões de tiros

Velocidade 808nm: comprimento de onda padrão dourado para todos os tipos de cabelo

Alex 755nm: Eficaz específico para cabelos loiros, cabelos finos

Pulso longo 1064nm: específico eficaz para pele escura e bronzada, melhor qualidade ipl shr opt laser/nd yag/alexandrite preço da máquina de depilação a laser

Modelo	laser de diodo 808
Tipo de Laser	Laser de diodo 808nm ou 755/808/1064 3 ondas
Mostrar	Sistema de tela sensível ao toque de 14 polegadas
Wavelength	808nm/7558081064
shots	20-40 milhões de tiros
Energia	10~150 j/cm2, ajustável
Frequency	1-10HZ
Cooling	Resfriamento TEC duplo
Power	3000W
Spot size	12*35mm ou 12*20mm para escolher
Tensão	110 V/60 HZ ou 220 V/50 HZ para escolher

perfil de companhia

1. A empresa Weifang Minliang tem 15 anos de experiência em fabricação de equipamentos de beleza em instrumento de beleza.

Foi vendido para 102 países e atende a mais de 600.000 instituições em todo o mundo. Facilite os negócios de beleza.

2. Apoio shell de máquina OEM, sistema de máquina OEM, pode adicionar seu próprio

logotipo....

3. Temos um departamento profissional de P & D de produção. A máquina de embalagem de caixa de alumínio é resistente e durável, com proteção de segurança, ajudando sua máquina a chegar em casa com segurança!

Packing

safe and thoughtful packaging seivice



Built-in prevention Collision bubble

Two-year warranty for machine handle as consumable, one-year warranty.

OEM&ODM service for distributor.

Tight packaging

Training: (Video+Manual+Online Service)
Can Keep You Operate It Easily.



3-5 business days delivery

Professional guide:
24 Hours Professional online customer service,

**Entre em contato conosco agora
24 horas online!**