



Diode Laser

Permanent hair removal

[Understand more](#)




14 inch
Screen Size



3000W
Input power



1-10HZ
Frequency



755nm 808nm 1064nm
Wavelength

>>Machine 14-inch large screen

>>3000W machine power to ensure the treatment effect

>>1-10Hz fast frequency and 15x25mm spot size ensures faster, smooth and effective treatment

>>808 single wave or 755nm/808nm/1064nm perfect triple wavelengths

>>Easy to operate Data Base system,can do the treatment by man mode and women mode,also different body part.To ensure a safe parameter for new operator
>> Long life time More than 40 millions shots gold laser diode module, anti high temperature.



HAIR REMOVAL

HAIR REMOVAL

350g lightweight **handle**, more ergonomic

Available in **black or white**



A alça pesa apenas 350g, o que é conveniente para o tratamento

>>12 pieces or 16 pieces Germany Dilas original laser bars,600/800W/1200W power is capable to meet all demands of hair removal on the whole body;
>>1-10Hz fast frequency and 15x25mm spot size ensures faster, smooth and effective treatment;

>Super sapphire touch cooling system ensures painless and comfortable treatment

The collage includes:
1. A diagram titled "Hair removal principle" showing three stages of hair growth and the laser's effect on the melanin in the hair follicle.
2. A woman's legs, one smooth and one with hair, demonstrating the results of hair removal.
3. Three women of different skin tones (light, medium, dark) labeled I, II, and III, corresponding to the laser wavelengths 755 nm, 808 nm, and 1064 nm respectively.
4. A color-coded legend at the bottom left indicating the wavelength for each skin type: 755 nm (light beige), 808 nm (medium beige), and 1064 nm (dark brown).

755 nm for white skin (fine, golden hair removal);

808 nm for yellow neutral skin (brown hair removal);

1064 nm for black skin (black hair removal)

Lidar com tempo de vida longa 20-40 milhões de tiros

Velocidade 808nm: comprimento de onda padrão dourado para todos os tipos de cabelo

Alex 755nm: Eficaz específico para cabelos loiros, cabelos finos

Pulso longo 1064nm: específico eficaz para pele escura e bronzeada, melhor qualidade ipl shr opt laser/nd yag/alexandrite preço da máquina de depilação a laser

Export 102 countries+

102 countries, 60,000+ customers

