



Преимущество машины для удаления волос с диодным лазером 755 808 1064

- 1) Используйте конденсатор ТЕС, он имеет лучший охлаждающий эффект, убедитесь, что машина работает непрерывно 24 часа, даже летом.
- 2) Используйте насос высокого давления, импортированный из Италии, срок службы на 40 000 000 больше.
- 3) 2 фильтра, 1 фильтр для умягчения воды, 1 фильтр для очистки от примесей.
- 4) Высокая мощность 2000 Вт, сильная энергия, хороший эффект удаления волос.

MULTI-ANGLE MACHINE DISPLAY



New upgrade 14-inch HD 4K screen
12*35mm big spot size
Optional parameters for different skin types



ADVANTAGE

- **PAINLESS:**755/808/1064nm diode laser for all type skin hair removal
- **FASTER:**Large area spot sliding operation
- **NO TRAUMA:**There is no trauma to skin tissue
- **SAFETY:**To avoid the light of the deputy to reduce the difficulty of operation



Before and After

Treatment comparison



• *Cooling effect* •

The handle is frosted for one minute,
making your treatment more comfortable and painless



Suitable for hair removal on any part of the body,
Such as arms, legs, face, armpits, back, chest, etc.



TECHNICAL PARAMETERS

Device Name	Diode laser hair removal machine
Model Number	V30 single handle 4K
Wavelength	755nm 808nm 1064nm
Screen size	14 inch 4K true color touch screen
Pulse Duration	1-300ms
Frequency	1-10hz
Spot size	12*35mm
Energy	1-150J/cm2
Cooling	Water cooling+Air cooling
Voltage	AC220V/110V 50HZ/60HZ
Demension of machine	45.4cm*52.1cm*101cm
Package	Aluminum box
Warranty	2 years

Для получения дополнительной информации о продукте, пожалуйста, свяжитесь с нами 24 часа онлайн!