

MLKJ

CUSTOMER SERVICE

15 YEARS FACTORY, 2 YEARS WARRANTY, 102 COUNTRIES, 60,000+ CUSTOMERS.

MLKJ—MAKE YOUR BEAUTY BUSINESS EASIER



15 years factory



2 years warranty



102 COUNTRIES



2 years warranty




14 inch
Screen Size



3000W
Input power



1-10HZ
Frequency



755nm 808nm 1064nm
Wavelength

>>Machine 14-inch large screen

>>3000 Вт machine Власть to ensure the treatment effect

>>1-10 Гц fast Частота and 15x25mm Размер пятна ensures faster, smooth and effective treatment


>>808 single wave or 755nm/808nm/1064nm perfect triple Длина волны

>>Easy to operate Data Base system,can do the treatment by man mode and women mode, также

другая часть тела. Чтобы обеспечить безопасный параметр для нового оператора
>> Long life time More than 40 millions выстрелы gold laser diode module, anti high temperature.

350g lightweight handle, more ergonomic

Available in **black or white**



Ручка весит всего 350 г, что удобно для лечения.

>>12 pieces or 16 pieces Germany Dilas original laser bars,600/800W/1200W power is capable to meet all demands of hair removal on the whole body;

>>1-10Hz fast frequency and 15x25mm spot size ensures faster, smooth and effective treatment;
 >Super sapphire touch Охлаждение system ensures painless and comfortable treatment;



Hair removal principle

Make Your Beauty Business More Easier



The laser selectively acts on the melanin in the hair follicle, destroying the hair-growing area

Natural hair loss, prevent regeneration, and achieve the purpose of hair removal


Hair removal also stimulates collagen regeneration, shrinks pores and makes skin firm and smooth



755 nm



808 nm



1064 nm

-  755 nm for white skin (fine, golden hair removal);
-  808 nm for yellow neutral skin (brown hair removal);
-  1064 nm for black skin (black hair removal)

Ручка Долгий срок службы 20-40 миллионов выстрелов

Скорость 808 нм: золотой стандарт длины волны для всех типов волос

Alex 755nm: специально эффективен для светлых и тонких волос.

Длинный импульс 1064 нм: специально эффективен для темной, загорелой кожи, лучшее качество, лазер ipl shr opt / nd yag / александритовый лазер, цена машины для удаления волос







| | |
|------------|---|
| Модель | 808V27- диодный лазер |
| Тип лазера | Диодный лазер 808 нм или 755/808/1064 3 волны |
| Отображать | Система с 14-дюймовым сенсорным экраном |
| Wavelength | 808нм/7558081064 |
| shots | 20-40 миллионов выстрелов |
| Энергия | 10~150 Дж/см ² , регулируемая |
| Frequency | 1-10HZ |
| Cooling | Двойное TEC-охлаждение |
| Power | 3000W |
| Spot size | 12*35 мм или 12*20 мм на выбор |
| Напряжение | 110 В/60 Гц или 220 В/50 Гц на выбор |

Профиль Компании

1. Компания Weifang Mingliang имеет 15-летний опыт производства косметического оборудования. в инструменте красоты.

Он был продан в 102 страны и обслуживает более 600 000 учреждений по всему миру. Сделайте бизнес в сфере красоты проще.



2. Поддержка OEM-оболочки машины, OEM-система машины, можно добавить свой собственный логотип....

3. У нас есть профессиональный производственный отдел исследований и разработок. Упаковочная машина для алюминиевых коробок прочная и долговечная, с защитой безопасности, помогая вашей машине безопасно вернуться домой!

Packing

safe and thoughtful packaging service



Built-in prevention Collision bubble

Two-year warranty for machine handle as consumable,
one-year warranty.

OEM&ODM service for distributor.

Tight packaging

Training: (Video+Manual+Online Service)
Can Keep You Operate It Easily.



3-5 business days delivery

Professional guide:
24 Hours Professional online customer service,

**Свяжитесь с нами сейчас
24 часа онлайн!**