

# NEW ! Technology



Преимущество машины для удаления волос с диодным лазером Titanium 1600 Вт

1. 7558081064нм система удаления волос диодного лазера использует, подходит для всех типов кожи удаления волос.
2. Золотые лазерные стержни, импортированные из Германии или США, срок службы до 40 000 000 больше.
3. Система охлаждения 1600WTEC, обеспечивающая непрерывную работу лазера без кондиционера летом
4. Без шрамов, без побочных эффектов.
5. Высокая мощность, без боли, 3-5 сеансов постоянного удаления волос

One minute cooling -21°C



Best **TEC Cooling** system  
hair remover laser




**12\*20mm** or **12\*35mm** handle

Suitable for any unwanted hair on areas like face, arms, armpits, chest, back, bikini, legs...



1 минута лечения ☐☐



**NEW !  
Technology**




# High-quality laser bars imported from USA

1000/1200/1600ww high power



Fast hair removal



▶ 10bar  
**1000W**




▶ 12bar  
**1200W**



▶ 16bar  
**1600W**



# For all skin types



755nm / 808nm / 1064 nm

**The handle equipped with 3 wavelength: Alex 755nm, speed 808nm and long pulse 1064nm**

**Speed 808nm:** Golden standard wavelength for all hair types

**Alex 755nm:** Specific effective for blonde hair, fine hair

**Long Pulse 1064nm:** Specific effective for dark, tanned skin



Система охлаждения 3 в 1: Воздушное охлаждение водяное охлаждение охлаждение TEC  
Система 3 в 1. 24 часа работы.

12 \* 20 мм / 12 \* 35 мм большой размер пятна, сокращение времени обработки для оригинала 1/5



## Large Spot Size

### Quick and Comfortable

With large spot size of  $1.2 \times 3.5 \text{cm}^2$ , for faster treatments and better patient experience.



## TEC Plus

### Continuous Contact Cooling

TEC is an advanced technology that continuously cools skin and facilitates range-controlled temperature throughout the entire treatment. Patients can now enjoy a completely pain-free, cool and comfortable experience throughout the session.



- \* 12,4/14 дюймов Сенсорный экран True Color, предлагающий очень крутой сенсорный опыт.
- \* OEM сервис принимается. регулировка параметра в порядке.
- \* Добавьте свой логотип и язык бесплатно

# The new 14-inch screen is clear easy to operate.



**OEM/ODM SERVICE**

Спецификация Аппарат для удаления волос с диодным лазером Titanium 1600 Вт

Элемент	Вертикальный диодный лазер 755нм808нм1064нм
Тип лазера	Диодный лазер, 10бар 12бар/16бар
Мощность каждого бара	100 Вт/бар
Система отображения	12,4/14-дюймовый сенсорный экран истинного цвета
Длина волны	808нм/755нм/1064нм
Размер пятна	12*20мм²/12*35мм²
Срок службы лазерной ручки	Не менее 20-40 миллионов выстрелов