



### **Особенности пикосекундного лазера**

- >>No injury to skin and hair follicle; no risk of scarring.
- >>Instantaneous blasting high laser technology, international standard of production, technical test strictly.
- >>Imported stone Q-switch cassette mechanism, the entire solid laser, without replacing Q-switch.
- >>Painless treatment, little side-effect.



# HANDLE-ADVANTAGE



## specification

- **Multiple choice**  
fixed 1064nm & 532nm, adjustable 1064nm&532nm(adjust 1-7 mm)for tattoo removal,nevus removal etc.
- **Multifunction**  
1320nm for skin rejuvenation
- **Indicator light**  
Dot position is the indicator light position dot more accurate



Adjustable  
532nm



Adjustable  
1064nm



Black doll  
1320nm



Fixed  
755nm



Fixed  
532nm



Fixed  
1064nm




Шесть головок регулируют размер пятна от 1 мм до 7 мм.

Регулируемый 1064nm/532nm, фиксированный 1064nm/532nm/1320nm/755nm.

- \* Фиксированные 1064/532 нм, используемые для удаления татуировок, удаления линии губ, удаления бровей, удаления невуса Ота, удаления грибка ногтей.
- \* Фиксированная длина волны 1320 нм используется для отбеливания кожи, сужения пор, подтяжки кожи.
- \* Фиксированная длина волны 755 нм используется для отбеливания кожи, удаления желтой кожи, хлоазмы, возрастного пигмента.
- \* Регулируемая длина волны 1064/532 нм, используемая для быстрой обработки больших площадей, регулируемый размер пятна 1-7 мм.

# Screen Display

The display screen is clear at a glance and easy to operate



**8.4 inch true color big touch screen.** Super cool touch Experience.  
**Special language** can be added according to your actual requirements.  
**Your logo** also can be added on diode laser screen.

**Сравнение эффектов**

# Treatment **Effec**

Tattoo removal

Nevus Ota removal

Eyebrow and eyeline removal

Lipline removal



Параметры продукта

APPLICATION	1)Tattoo removal 2)Eyebrow embroidery removal 3)Eyeline removal 4)Freckles removal 5)Skin rejuvenation 6)Lipline removal 7)Pigment treatment 8)Whitening
wavelength	1064nm&532nm&755 nm & 1320nm &1064nm(Adjustable )&532nm(Adjustable )
Pulse energy	1-1500MJ/CM
Width of Pulse	0-10ns
Frequency	1-10HZ
Light spot	1-7mm
Power supply:	220V, 6A or 110V, 12A
color	Blue and black color
Packing method	Aluminum Packing
N.W	20kg
G.W	30kg
Machine	35cm*45cm*35cm(L*W*H)
Aluminum box	46*49*60cm(L*W*H)



Plastic foam:6cm



strong and beautiful  
aluminum alloy case



N.W 20KG



G.W 30KG

# Free logo service

