



755 808 1064 Diode Lazer Epilasyon Makinasının Avantajı

- 1) TEC kondansatör kullanın, daha iyi soğutma etkisine sahiptir, makinenin yazın bile 24 saat kesintisiz çalıştığından emin olun.
- 2) İtalya'dan ithal edilen yüksek basınç pompasını kullanın, 40.000.000 daha uzun kullanım ömrü
- 3) 2 Filtre, 1 filtre suyu yumuşatmak için, 1 filtre kirlilik için ayrı.
- 4) Yüksek güç 2000w, güçlü enerji, iyi epilasyon etkisi elde edin.

MULTI-ANGLE MACHINE DISPLAY



New upgrade 14-inch HD 4K screen
12*35mm big spot size
Optional parameters for different skin types



ADVANTAGE

- **PAINLESS:**755/808/1064nm diode laser for all type skin hair removal
- **FASTER:**Large area spot sliding operation
- **NO TRAUMA:**There is no trauma to skin tissue
- **SAFETY:**To avoid the light of the deputy to reduce the difficulty of operation



Before and After

Treatment comparison



• *Cooling effect* •

The handle is frosted for one minute,
making your treatment more comfortable and painless



Suitable for hair removal on any part of the body,
Such as arms, legs, face, armpits, back, chest, etc.



TECHNICAL PARAMETERS

Device Name	Diode laser hair removal machine
Model Number	V30 single handle 4K
Wavelength	755nm 808nm 1064nm
Screen size	14 inch 4K true color touch screen
Pulse Duration	1-300ms
Frequency	1-10hz
Spot size	12*35mm
Energy	1-150J/cm2
Cooling	Water cooling+Air cooling
Voltage	AC220V/110V 50HZ/60HZ
Demension of machine	45.4cm*52.1cm*101cm
Package	Aluminum box
Warranty	2 years

Daha fazla ürün bilgisi için lütfen 24 saat çevrimiçi olarak bizimle iletişime geçin!