

Picosure Laser

Picosecond Laser



Güzellik salonu musun? Distribütör? Yoksa bir ticaret şirketi mi?

Ürünler için OEM veya ODM'ye ihtiyacınız var mı?

Fabrikamız OEM ve ODM hizmetleri sunmaktadır.

En son fiyatları öğrenmek için lütfen bize soruşturma gönderin, hatta 24 saat!

Ürün Bilgisi

conten†



Teknik özellikler:

>>No injury to skin and hair follicle; no risk of scarring.

>>Instantaneous blasting high laser technology, international standard of production, technical test strictly.

>>Imported stone Q-switch cassette mechanism, the entire solid laser, without replacing Q-switch.

>>Painless treatment, little side-effect.

>>Easy to operate.



Pikosaniye lazer uygulaması:

1.Bu Pico ikinci lazer makinesi, çift lazer çubuğu ve yüksek güç kaynağı ile donatılmıştır. Işık, pigmentasyon çıkarma, dövme çıkarma, kaş temizleme ve cilt beyazlatma vb. işlerde iyi iş çıkarıyor. Ve etkisi, yaygın kullanılan nd yaglaser makinesinden daha iyi. (toplam 5 prob ile) 3 sabit 1064&532&1320nm&755nm,

2.Ayarlanabilir problemler 1064&532nm



Adjustable
532nm



Adjustable
1064nm



Black doll
1320nm



Fixed
755nm



Fixed
532nm



Fixed
1064nm



Working Principle



Pikosaniye lazer kolları:

>> 755nm: Pico second laser head, for age spot removal, freckle removal, chloasma removal.

>> 1064nm & 532nm for tattoo removal, eyebrow clearance, etc.

>> New brand guide light arm for tattoo laser removal machine, with a more delicate appearance.



Screen interfac

Professional Screen, Easy operation



24 saat çevrimiçi hizmet!