

NEW ! Technology



Titanyum 1600W Diod Lazer Epilasyon makinesinin avantajı

1. 7558081064nm diyot lazer epilasyon sistemi kullanır, Tüm cilt tiplerinde epilasyon için uygundur.
2. Almanya veya ABD'den ithal edilen altın lazer çubukları, maksimum 40.000.000 daha uzun ömür
3. 1600WTEC soğutma sistemi, yaz aylarında lazerin klima olmadan sürekli çalışmasını sağlar
4. Yara izi yok, herhangi bir yan etki yok.
5. Yüksek güç, ağrı yok, 3-5 seans kalıcı epilasyon

One minute cooling -21°C

Best **TEC Cooling** system
hair remover laser



12*20mm or **12*35mm** handle

Suitable for any unwanted hair on areas like face, arms, armpits, chest, back, bikini, legs...

12*20mm {




12*35mm {



1 dakikalık tedavi ☐☐



**NEW !
Technology**




High-quality laser bars imported from USA

1000/1200/1600ww high power



Fast hair removal



▶ 10bar
1000W




▶ 12bar
1200W



▶ 16bar
1600W

For all skin types



755nm / 808nm / 1064 nm

The handle equipped with 3 wavelength: Alex 755nm, speed 808nm and long pulse 1064nm

Speed 808nm: Golden standard wavelength for all hair types

Alex 755nm: Specific effective for blonde hair, fine hair

Long Pulse 1064nm: Specific effective for dark, tanned skin



3'ü 1 arada soğutma sistemi: Hava Soğutma Su Soğutma TEC Soğutma 3'ü 1 Arada Sistem.24 saat çalışma yeteneği

12*20mm / 12*35 mm Büyük Nokta Boyutu, orijinal 1/5 için tedavi süresini azaltın



Large Spot Size

Quick and Comfortable

With large spot size of $1.2 \times 3.5 \text{cm}^2$, for faster treatments and better patient experience.



TEC Plus

Continuous Contact Cooling

TEC is an advanced technology that continuously cools skin and facilitates range-controlled temperature throughout the entire treatment. Patients can now enjoy a completely pain-free, cool and comfortable experience throughout the session.



- * 12,4 /14 inç Gerçek Renkli Dokunmatik Ekran, süper harika dokunma deneyimi sunar.
- * OEM hizmeti kabul edildi. ayar parametresi tamam.
- * Logonuzu ve dilinizi ücretsiz ekleyin

The new 14-inch screen is clear
easy to operate.



OEM/ODM SEVRICE

Şartname Titanyum 1600W Diod Lazer Epilasyon makinesi

Öge	Dikey 755nm808nm1064nm diyot lazer
lazer tipi	Diyot lazer, 10 bar 12 bar/16 bar
Her çubuğun gücü	100w/çubuk
Ekran sistemi	12,4 /14 inç gerçek renkli dokunmatik ekran
dalga boyu	808nm/755nm/1064nm
Spot Büyüklüğü	12*20mm²/12*35mm²
Lazer sap ömrü	En az 20-40 milyon atış