



Household A1

Three bands: 755nm/808nm/1064nm

Suitable for all skin tones

Laser painless hair removal

Tařınabilir ev tipi epilasyon makinesi avantajları

- 1) Makinenin toplam hacminin çok küçük olduėunu g steriniz.
- 2) Ekran tutacaėı k   kt r, 168g tutma yeri  ok hafiftir
- 3) Makine, y ksek soėutma verimliliėine ve d ř k g r lt ye sahip bir kompres rd r.
- 4) Makine hafiftir ve tařıması kolaydır



Machine Parts



Handle Display

*The handle is small and light, weighing as low as 168.8g.
Very light to operate*



Machine Display



Left 45°



Positive



Right 45°

Mini Diyot Lazer kolu, spot boyutu 14*14mm, 5 bar 600w

Cooling Effect

The handle has a cooling effect that improve treatment comfort.



Just One minute!

Quick cooling down to

-25°C

1) Diyot lazer 755nm808nm 1064nm, tüm cilt tipleri için epilasyon

2) Ağrısız epilasyon için su soğutma Hava soğutma kompresör soğutma.

Working Principle

755nm and 808nm and 1064nm , suits for all skin and hair types.



ALEX 755nm

For white skin

(fine, golden hair removal)



SPEED 810nm

For yellow neutral skin


(brown hair removal)



YAG 1064nm

For black skin


(black hair removal)



Screen Display

13.3 inch 4K true color touch screen

The display screen is clear at a glance and easy to operate



6 language for your choice. Super cool touch Experience .

Special language can be added according to your actual requirements.

Your logo also can be added on diode laser screen.

1. 13,3 inç dokunmatik ekran, insanlaştırılmış tasarım
2. Erkek/dişi, vücut parçaları, seçenek için 6 cilt tipi.
3. İngilizceana diliniz.
4. Ücretsiz OEM program servisi(logo/sistem...)

We have OEM Services

Serving your needs



Fabrikamız

Weifang Sunshinekj elektronik Co, Ltd (kısaltma: MLKJ) Çin'de son derece profesyonel ve deneyimli bir güzellik ekipmanı üreticisidir, güzellik endüstrisinde 14 yıldır

13 Years Laser Beauty Decvice Manuafactor

- High Feedback
Top10 Supplier
- **OEM & ODM**
SERVICE



13 Years Laser Beauty Decvice
Manuafactor



• High Feedback
Top10 Supplier

• OEM & ODM
SERVICE

Premium OEM Factories

High-performance manufacturing capacity
R&D capability for customization
Professional certifications and approvals

2.Profesyonel Üretim Ar-Ge departmanımız var, teknik destek sağlayabiliriz, 2 yıl garanti



Product Customization Design



Production and Processing



Program Debugging



Machine Debugging



Batch Production



Fine and Safe Packaging

Ürün paketleme

Packing

safe and thoughtful packaging service



Built-in prevention Collision bubble

Two-year warranty for machine handle as consumable,
one-year warranty

OEM&ODM service for distributor.

Tight packaging

Training: (Video+Manual+Online Service)

Can Keep You Operate It Easily



3-5 business days delivery

Professional guide:

24 Hours Professional online customer service