



### **Pikosaniye Lazer Özellikleri**

- >>No injury to skin and hair follicle; no risk of scarring.
- >>Instantaneous blasting high laser technology, international standard of production, technical test strictly.
- >>Imported stone Q-switch cassette mechanism, the entire solid laser, without replacing Q-switch.
- >>Painless treatment, little side-effect.



# HANDLE-ADVANTAGE



## specification

- **Multiple choice**  
fixed 1064nm & 532nm, adjustable 1064nm & 532nm (adjust 1-7 mm) for tattoo removal, nevus removal etc.
- **Multifunction**  
1320nm for skin rejuvenation
- **Indicator light**  
Dot position is the indicator light position dot more accurate



Adjustable  
532nm



Adjustable  
1064nm



Black doll  
1320nm



Fixed  
755nm



Fixed  
532nm



Fixed  
1064nm



Altı kafa, spot boyutunu 1 mm'den 7 mm'ye ayarlar.

Ayarlanabilir 1064nm/532nm, sabit 1064nm/532nm/1320nm/755nm.

- \* Dövmе silme, dudak çizgisi kaldırma, kaş kaldırma, Nevus of Ota çıkarma, tırnak mantarı çıkarma için kullanılan sabit 1064/532 nm.
- \* Cilt beyazlatma, gözenek küçültme, cilt kaldırma için kullanılan sabit 1320 nm.
- \* Cilt beyazlatma için kullanılan sabit 755 nm, sarı cildi, kloazmayı, yaş pigmentini çıkarın
- \* Ayarlanabilir 1064/532 nm, geniş alan hızlı tedavi için kullanılır, nokta boyutu 1-7mm ayarlanabilir.

# Screen Display

The display screen is clear at a glance and easy to operate



**8.4 inch true color big touch screen.** Super cool touch Experience.  
**Special language** can be added according to your actual requirements.  
**Your logo** also can be added on diode laser screen.

**Etki Karşılaştırması**

# Treatment **Effec**

Tattoo removal

Nevus Ota removal

Eyebrow and eyeliner removal

Lipline removal



Ürün parametreleri

|                |                                                                                                                                                                               |
|----------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| APPLICATION    | 1)Tattoo removal<br>2)Eyebrow embroidery removal<br>3)Eyeline removal<br>4)Freckles removal<br>5)Skin rejuvenation<br>6)Lipline removal<br>7)Pigment treatment<br>8)Whitening |
| wavelength     | 1064nm&532nm&755 nm &1320nm<br>&1064nm(Adjustable )&532nm(Adjustable )                                                                                                        |
| Pulse energy   | 1-1500MJ/CM                                                                                                                                                                   |
| Width of Pulse | 0-10ns                                                                                                                                                                        |
| Frequency      | 1-10HZ                                                                                                                                                                        |
| Light spot     | 1-7mm                                                                                                                                                                         |
| Power supply:  | 220V, 6A or 110V, 12A                                                                                                                                                         |
| color          | Blue and black color                                                                                                                                                          |
| Packing method | Aluminum Packing                                                                                                                                                              |
| N.W            | 20kg                                                                                                                                                                          |
| G.W            | 30kg                                                                                                                                                                          |
| Machine        | 35cm*45cm*35cm(L*W*H)                                                                                                                                                         |
| Aluminum box   | 46*49*60cm(L*W*H)                                                                                                                                                             |



Plastic foam:6cm



strong and beautiful  
aluminum alloy case



N.W 20KG



G.W 30KG

# Free logo service

